






Attaching elastic to slips and bed sheets W664-81ACx356/RP113A/MD520

For W664–81, subclass for attaching elastic to bed sheets, we use the new metering device MD520. This new metering device guarantees very accurate metering of the elastic.

The new MD – controller MD520, is basically the same principle like MD440 and the operator panel is also very similar to the small and easy to operate MD440 – operator panel:

- 26 programs are available
- 1 seam within each program
- 2 different tensions can be pre-selected and applied by knee switch in any order.

【MD520】



Example



*Showing
W664-81Acx356/RP113A/MD520
with front bottom metering device*

*Remark:
Folder has to be arranged, according to
elastic width and style of fabric folding*

Further features of W664-81/MD520:

- ✓ Easy programming
- ✓ Wide variety of elastic and fabric and different tension can be used, due to high flexibility of stepping motor controlled metering device.
- ✓ High productivity, due to no speed restrictions from the stepping motor controlled metering device
- ✓ It takes ~ 45 seconds to attach elastic to single bed size bed sheet
- ✓ Mechanic level for technicians is integrated in the controller.



Control panel of MD520

The controller responds to CE-regulations and is manufactured in Japan to provide high quality and reliability.